

# ACT2016SMX-4

The ACT2016SMX-4 is an extremely compact, high quality, low aging, seam welded crystal. Utilising a ceramic base with a metal lid, it provides for the durability and reliability, necessary for strenuous processes like infrared and vapour reflow. The lid is grounded through the package, to assist with EMC Issues, and the pads are gold plated. The device is very suitable for automatic placement on PCB's. With an excellent range of frequencies and stabilities it is an optimum choice for designs where PCB space is at a premium. Applications include: PDA, Cellular, MPU Clocks, ISM, Bluetooth, WLan, and consummer electronics. Available loose or on reels (Standard 3,000 pieces / reel.).





### **Specification**

Parameter	Symbol	Specification	Condition
Frequency Range	fo	24.00 ~ 60.00 MHz AT Fundamental	Please specify
Frequency Tolerance	∆f/fo	±10ppm ~ 30ppm @25°C±3°C (refer to table 2)	Please Specify
Stability over Temp Range	Тс	±10ppm ~ 30ppm (refer to table 2)	Please specify
Temp Operating Range	Topr	-20 ~ +70°C Standard (refer to table 2)	Please specify
Temp Storage Range	Tstg	-40 ~ +85°C	
Equivalent Series Resistance	ESR	Please refer to Table 1	
Load Capacitance	CL	8 ~ 12pF	Please specify
Shunt Capacitance	C0	7pF max	
Drive Level	DL	50μW typical (100μW max)	
FDLD		≤+/-30% ESR	20 steps
RDLD		≤+/-10ppm	20 steps
Insulation Resistance	IR	500M $Ω$ min	@100V DC
Reflow Process		10 Seconds @ 260°C (max)	
Aging	Fa	±2ppm / 1st year max	@25°C




Table 1

Frequency(MHz)	$ESR\Omega\;max$	Mode	
24.0~24.999	100	Fundamental	
25.0~35.999	80	Fundamental	
36.0~60.000	60	Fundamental	

Pad surface material Au

# Standard frequencies (MHz):

24.000, 26.000, 32.000, 38.400, 40.000, 48.000

Table 2

		±10ppm	±20ppm	±30ppm
Tolerance	25°C			$\square$
Stability	-20~+70°C	$\square$	$\overline{\square}$	$\square$
	-40~+85°C		✓	$\square$

Please note that all parameters can not necessarily be specified in the same device

Customer to specify: Frequency, Frequency Tolerance, Temperature Stability, Operating Temperature & Load Capacitance In line with our ongoing policy of product evolvement and improvement, the above specification may be subject to change without notice

## ISO9001:2000 Registered

For quotations or further information please contact us at: 3 The Business Centre, Molly Millars Lane, Wokingham, Berkshire, RG41 2EY, UK


http://www.actcrystals.com




Tel: 0044 (0)118 979 1238 Fax: 0044 (0)118 979 1283 email: info@actcrystals.com

ACT2016SMX-4 Series Tape Dimensions (Units in mm)


\* Standard: 3.000 piece reels



# Tape and Reel Dimensions (mm)



# **Reflow Information**



In line with our ongoing policy of product evolvement and improvement, the above specification may be subject to change without notice

#### ISO9001:2000 Registered

For quotations or further information please contact us at:


3 The Business Centre, Molly Millars Lane, Wokingham, Berkshire, RG41 2EY, UK

http://www.actcrystals.com



Tel: 0044 (0) 118 979 1238 Fax: 0044 (0) 118 979 1283 email: info@actcrystals.com

### SERIES: ACT2016SMX-4 Part numbering code is CX



#### **NOTES:**

- Tighter Tolerances and Stabilities and other Operating Temperature Ranges may be available.
   As each of these specification parameters impact on each other, it is not always possible to combine all options in one device. Therefore, if a specification not catered for above is required, please contact us directly for the relevant part number code(s).
- 2) ACT are always happy to consider truly custom specification parts which may require non-standard specification parameters, specific testing, customer requested AQL requirements, non standard packaging or taping and reeling and custom marking. Such devices would normally be allocated a custom specification part number which is wholly customer specific.
  (FC. A.24.00MHz sustomer ACT2016MM 4 doubte may have a part number such as CY2400C, C4123 PE).
  - ( EG : A 24.00MHz custom ACT2016MX-4 device may have a part number such as CX2400C- C1133-PF)
- 3) A guide to availability of tighter stabilities appears in Table 2 of the data sheet